

**Garant****GARANT Master Tap machine tap HSS-E-PM extra long Form C 6HX, AlTiX, M: M6****Order data**

Order number	134680 M6
GTIN	4045197901231
Item class	11I

**Description****Version:**

**Universal taps**, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for a high degree of wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

With extra long shank. **Shank to DIN 371.**

**Advantage:**

Designed for tapping threads where access is difficult.

**Technical description**

Thread size	M6
Thread pitch	1 mm
Tool material	HSS E PM
Thread Ø	6 mm
Tapping hole Ø	5 mm
Number of clamping slots	3
Shank square □	4.9 mm
Overall length L	160 mm
Tolerance class	ISO 2X 6HX
Number of cutting edges Z	3

Thread depth	15 mm
Shank $\varnothing D_s$	6 mm
Standard	Manufacturer's standard
Thread type	M
Coating	AlTiX
Flank angle	60 degrees
Thread standard	DIN 13
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	28 m/min	N
Alu > 10% Si	suitable	16 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	24 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	24 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	20 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	10 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	6 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	8 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable	6 m/min	M
GG(G)	suitable	16 m/min	K
CuZn	suitable	16 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		