

**Garant**
**Solid carbide milling cutter Composite, dragging cut, uncoated, Ø h10 DC: 10mm**

**Order data**

Order number	209540 10
GTIN	4062406362539
Item class	100

**Description**
**Version:**

**Tool cutting edge has been specifically developed further** for optimum machining of composite materials.<br>Length similar to **DIN 6527 long**.

Right-hand helix, **dragging cut** for standard applications.

**Technical description**

Helix angle	8 degrees
Shank Ø D <sub>s</sub>	10 mm
Feed f <sub>z</sub> for slot milling in GRP CRP	0.035 mm
Overall length L	72 mm
Direction of infeed	horizontal, oblique and vertical
Overhang length L <sub>1</sub> incl. recess	30 mm
Flute length L <sub>c</sub>	22 mm
Recess Ø D <sub>1</sub>	9.7 mm
Cutting edge Ø D <sub>c</sub>	10 mm
Tolerance nominal Ø	h10
Corner chamfer width at 45°	0.2 mm
Shank	DIN 6535 HA to h6

No. of teeth Z	8
Corner chamfer angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	black
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
PVDF GF20	suitable	80 m/min	N
POM GF25	suitable	80 m/min	N
PA 66 GF30	suitable	80 m/min	N
PEEK GF30	suitable	80 m/min	N
PTFE CF25	suitable	80 m/min	N
PEEK CF30	suitable	80 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	165 m/min	N
CRP	suitable	120 m/min	N
GRP, CRP	suitable	120 m/min	N
Graphite	suitable	180 m/min	N
wet maximum	suitable		
dry	suitable		
Air	suitable		