

**Garant**
**Solid carbide torus cutter R1 0.3, Diamond, Ø DC × L1: 2,5X50mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 209726 2,5X50 |
| GTIN         | 4045197919311 |
| Item class   | 10Y           |

**Description**
**Version:**

With **crystalline diamond sp<sup>3</sup> coating**. For the **highest demands regarding performance and precision** in fibre-reinforced composites, CRP, GRP, and graphite. **Extremely tight tolerances** ensure maximum accuracy. Double relief ground with 2 hollow-ground chamfers. **Recess angle  $\alpha = 16^\circ$** .

Tolerances:

- **Corner radius:  $R_1 = \pm 0.0025$  mm**
- **Neck Ø:  $D_1 = 0 / -0.01$  mm**

**Note:**

At greater tool overhang lengths, use a reduced value for  $a_p$ !

Values for:

copying:  $a_p = 0.10 \times D \times a_{p \text{ korr}}$

side milling:  $a_p = 0.20 \times D \times a_{p \text{ korr}}$

**To calculate the feed rate  $vf$  please use the actual speed of the machine (the maximum possible speed)!**

e.g:  $vf = 18000 \text{ [rpm]} \times fz \text{ [mm/Z]} \times z$

**Technical description**

|                      |                   |
|----------------------|-------------------|
| Corner radius $R_1$  | 0.3 mm            |
| Shank                | DIN 6535 HA to h5 |
| Cutting edge Ø $D_c$ | 2.5 mm            |
| Recess Ø $D_1$       | 2.41 mm           |
| Flute length $L_c$   | 2.5 mm            |
| Shank Ø $D_s$        | 4 mm              |

|                                                    |                                  |
|----------------------------------------------------|----------------------------------|
| Overall length L                                   | 90 mm                            |
| Overhang length L <sub>1</sub> incl. recess        | 50 mm                            |
| No. of teeth Z                                     | 2                                |
| Feed f <sub>z</sub> for copy milling in graphite   | 0.02 mm                          |
| Feed f <sub>z</sub> for side milling in graphite   | 0.02 mm                          |
| Helix angle                                        | 30 degrees                       |
| Correction factor a <sub>p corr</sub>              | 0.04                             |
| Coating                                            | Diamond                          |
| Tool material                                      | Solid carbide                    |
| Standard                                           | Manufacturer's standard          |
| Tolerance nominal Ø                                | 0 / -0.005                       |
| Direction of infeed                                | horizontal, oblique and vertical |
| Cutting width a <sub>e</sub> for milling operation | 0.5×D for side milling           |
| Cutting width a <sub>e</sub> for milling operation | 0.05×D for copy milling          |
| Through-coolant                                    | no                               |
| Colour ring                                        | black                            |
| Type of product                                    | Torus cutter                     |

## User data

|                    | Suitability | V <sub>c</sub> | ISO code |
|--------------------|-------------|----------------|----------|
| PVDF GF20          | suitable    | 200 m/min      | N        |
| POM GF25           | suitable    | 190 m/min      | N        |
| PA 66 GF30         | suitable    | 170 m/min      | N        |
| PEEK GF30          | suitable    | 150 m/min      | N        |
| PTFE CF25          | suitable    | 180 m/min      | N        |
| PEEK CF30          | suitable    | 160 m/min      | N        |
| Hybrids            | suitable    |                |          |
| Honeycomb sandwich | suitable    | 350 m/min      | N        |
| GRP                | suitable    | 190 m/min      | N        |

|             |          |           |   |
|-------------|----------|-----------|---|
| GRP, CRP    | suitable | 190 m/min | N |
| Graphite    | suitable | 340 m/min | N |
| wet minimum | suitable |           |   |
| dry         | suitable |           |   |
| Air         | suitable |           |   |