

Garant**GARANT Master Alu SlotMachine solid carbide roughing end mill with through-coolant HPC, DLC, Ø e8 DC: 10mm****Order data**

Order number	205255 10
GTIN	4062406122379
Item class	11X

Description**Version:**

For roughing.

Special profile for machining non-ferrous metals.

Improved chip evacuation due to central through-coolant.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Up to $2 \times D$ into solid material at very high feed rates and smooth cutting action.

Ramping capability up to 45° .

Very high feed rates when plunging vertically, thanks to **special plunging geometry**.

Note:

For **HB** shanks use order **No. 205256**.

Technical description

Helix angle	35 degrees
Overall length L	72 mm
Feed f_z for slot milling in short-chipping aluminium	0.12 mm
Shank $\varnothing D_s$	10 mm
Flute length L_c	22 mm
No. of teeth Z	3
Direction of infeed	horizontal, oblique and vertical

Overhang length L_1 incl. recess	30 mm
Balance quality with shank	G 2.5 with HA
Shank	DIN 6535 HA to h6
Feed f_z for side milling in short-chipping aluminium	0.14 mm
Cutting edge $\varnothing D_c$	10 mm
Recess $\varnothing D_1$	9.5 mm
Tolerance nominal $\varnothing$	e8
Corner rounding r_v	0.32 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	yes
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	450 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	380 m/min	N

PA 66	suitable only under restricted conditions	120 m/min	N
PEEK	suitable only under restricted conditions	100 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
Air	suitable		