



## Tap wrench, adjustable, Type: 5



### Order data

Order number	148410 5
GTIN	4062406210427
Item class	12L

### Description

#### Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **standard** use: Zinc die-cast body.

### Technical description

for hand taps DIN 352	M12 – M33
Overall length	700 mm
for hand reamer Ø DIN 206	9 - 26 mm
Capacity <input type="checkbox"/>	7 - 20 mm
Standard	DIN 1814
Type of product	Tap wrench