

Garant

GARANT Master Steel solid carbide finishing cutter HPC, TiAlN, Ø f8 DC: 16mm



Order data

Order number	204019 16
GTIN	4045197954251
Item class	11X

Description

Version:

For **finishing operations**.

Special geometry for optimum chip evacuation.

Unequal spacing gives high **intrinsic stability and smooth cutting action**.

For **profile milling as a finishing operation**.

Particularly long cutting edges for efficient finishing.

Note:

Can be reground from $\varnothing D_c = 6$ mm.

$a_{e\max} = 0.05 \times D$

Technical description

Balance quality with shank	G 2.5 with HA
Direction of infeed	horizontal
Flute length L_c	80 mm
Feed f_z for side milling in steel < 900 N/mm ²	0.105 mm
Shank	DIN 6535 HA to h6
Cutting edge $\varnothing D_c$	16 mm
Overall length L	136 mm
No. of teeth Z	7
Helix angle	45 degrees

Tolerance nominal \varnothing	f8
Shank $\varnothing D_s$	16 mm
Corner chamfer angle	90 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.05 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	200 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable	150 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M
GG(G)	suitable	200 m/min	K
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		

dry	suitable only under restricted conditions
Air Services	suitable
Shank grinding Type HB	129100 HB