

Garant
GARANT Master Tap machine tap HSS-E-PM extra long Form B 6HX, AlTiX, M: M10

Order data

Order number	131770 M10
GTIN	4045197901347
Item class	111

Description
Version:

Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for a high degree of wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Shank to DIN 371.

Advantage:

Designed for tapping threads where access is difficult.

Technical description

Thread type	M
Tolerance class	ISO 2X 6HX
Thread \varnothing	10 mm
Number of clamping slots	3
Shank square \square	8 mm
Tapping hole \varnothing	8.5 mm
Thread size	M10
Standard	Manufacturer's standard
Thread pitch	1.5 mm
Overall length L	200 mm

Thread depth	30 mm
Number of cutting edges Z	3
Tool material	HSS E PM
Shank $\varnothing D_s$	10 mm
Coating	AlTiX
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	28 m/min	N
Alu > 10% Si	suitable	16 m/min	N
Steel < 500 N/mm ²	suitable	24 m/min	P
Steel < 750 N/mm ²	suitable	24 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	10 m/min	P
Steel < 1400 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	8 m/min	M

INOX > 900 N/mm ²	suitable	6 m/min	M
GG(G)	suitable	16 m/min	K
CuZn	suitable	16 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		