

Garant**GARANT Master Alu SlotMachine solid carbide roughing end mill with through-coolant HPC, DLC, Ø e8 DC: 8mm****Order data**

Order number	205255 8
GTIN	4062406122362
Item class	11X

Description**Version:**

For roughing.

Special profile for machining non-ferrous metals.

Improved chip evacuation due to central through-coolant.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Up to $2 \times D$ into solid material at very high feed rates and smooth cutting action.

Ramping capability up to 45° .

Very high feed rates when plunging vertically, thanks to **special plunging geometry**.

Note:

For **HB** shanks use order **No. 205256**.

Technical description

No. of teeth Z	3
Tolerance nominal Ø	e8
Shank	DIN 6535 HA to h6
Shank Ø D _s	8 mm
Balance quality with shank	G 2.5 with HA
Feed f _z for slot milling in short-chipping aluminium	0.1 mm
Cutting edge Ø D _c	8 mm

Flute length L_c	19 mm
Helix angle	35 degrees
Recess $\varnothing D_1$	7.5 mm
Feed f_z for side milling in short-chipping aluminium	0.12 mm
Overhang length L_1 incl. recess	25 mm
Direction of infeed	horizontal, oblique and vertical
Overall length L	63 mm
Corner rounding r_v	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	yes
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	450 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	380 m/min	N

PA 66	suitable only under restricted conditions	120 m/min	N
PEEK	suitable only under restricted conditions	100 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
Air	suitable		