


Solid carbide milling cutter, uncoated, Ø e8 DC: 8mm

Order data

Order number	202239 8
GTIN	4045197964885
Item class	12X

Description
Version:

Eccentric relief ground, additionally **finish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Application:

For roughing and finishing.

Technical description

Feed f_z for side milling in short-chipping aluminium	0.04 mm
Cutting edge $\varnothing D_c$	8 mm
Tolerance nominal \varnothing	e8
Shank	DIN 6535 HA to h6
Feed f_z for slot milling in short-chipping aluminium	0.03 mm
No. of teeth Z	3
Shank $\varnothing D_s$	8 mm
Recess $\varnothing D_1$	7.5 mm
Helix angle	45 degrees
Direction of infeed	horizontal, oblique and vertical
Overall length L	70 mm
Flute length L_c	16 mm
Overhang length L_1 incl. recess	32 mm

Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	105 m/min	N
PMMA acrylic	Suitable	160 m/min	N
PE-HD	Suitable	110 m/min	N
PA 66	Suitable	130 m/min	N
PEEK	Suitable	110 m/min	N
PF 31	Suitable	90 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	160 m/min	N
Cu	Suitable	120 m/min	N
CuZn	Suitable	150 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	Suitable only under restricted conditions
Air	suitable only under restricted conditions
Services	
Shank grinding Type HB	129100 HB