

**Garant**
**GARANT Master INOX solid carbide milling cutter HPC / TPC, TiAlN, Ø h10 DC: 8mm**

**Order data**

Order number	202997 8
GTIN	4062406231590
Item class	11X

**Description**
**Version:**

For **roughing and finishing**.

HPC milling cutter with **newly developed high-performance coating** for **outstanding tool life** and **optimum metal removal rate** in a very wide range of stainless steels. **Greater oxidation resistance** and **high-temperature hardness**.

Can be used at **high cutting speeds**, particularly suitable even for TOOLOX®.

**Advantage:**

Particularly low vibration running.

**Technical description**

No. of teeth Z	4
Shank Ø D <sub>s</sub>	8 mm
Direction of infeed	horizontal, oblique and vertical
Flute length L <sub>c</sub>	19 mm
Recess Ø D <sub>1</sub>	7.5 mm
Overall length L	63 mm
Tolerance nominal Ø	h10
Shank	DIN 6535 HB to h6
Feed f <sub>z</sub> for side milling in INOX > 900 N/mm <sup>2</sup>	0.04 mm
Corner chamfer width at 45°	0.1 mm

Helix angle	40 degrees
Overhang length $L_1$ incl. recess	29 mm
Feed $f_z$ for slot milling in stainless steel $> 900 \text{ N/mm}^2$	0.025 mm
Cutting edge $\varnothing D_c$	8 mm
Corner chamfer angle	45 degrees
Series	Master INOX
Coating	TiAlN
Tool material	solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	$0.1 \times D$
Through-coolant	no
Machining strategy	TPC
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	250 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	230 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	200 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	180 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	115 m/min	P
Steel $< 50 \text{ HRC}$	suitable	80 m/min	H
INOX $< 900 \text{ N/mm}^2$	suitable	110 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable	90 m/min	M
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable only under restricted conditions		
Air	suitable		