




Solid carbide roughing end mill HPC, TiXSi, Ø f8 DC: 25mm



Order data

Order number	203044 25
GTIN	4045197679444
Item class	12X

Description

Version:

For **roughing and finishing**.

Up to 1.5×D into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Overhang length L_1 incl. recess	78 mm
Corner chamfer width at 45°	0.3 mm
Feed f_z for side milling in steel < 900 N/mm ²	0.16 mm
Recess Ø D_1	24.5 mm
Cutting edge Ø D_c	25 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.12 mm
No. of teeth Z	4
Shank Ø D_s	25 mm
Overall length L	136 mm
Flute length L_c	68 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8

Helix angle	38 degrees
Corner chamfer angle	45 degrees
Coating	TiXSi
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	250 m/min	P
Steel < 750 N/mm ²	suitable	200 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	160 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	70 m/min	M
GG(G)	suitable only under restricted conditions	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		

Air

suitable