

Garant
Solid carbide roughing end mill, uncoated, Ø d11 DC: 5mm

Order data

Order number	205330 5
GTIN	4045197878816
Item class	11X

Description
Version:
Dimensions similar to DIN 6527.
Knuckle form profile.
Special profile for machining non-ferrous metals.
Technical description

Overhang length L_1 incl. recess	20.5 mm
Feed f_z for side milling in short-chipping aluminium	0.045 mm
Cutting edge $\varnothing D_c$	5 mm
Overall length L	57 mm
Corner chamfer width at 45°	0.35 mm
No. of teeth Z	3
Recess $\varnothing D_1$	4.8 mm
Shank	DIN 6535 HB to h6
Feed f_z for slot milling in short-chipping aluminium	0.035 mm
Flute length L_c	13 mm
Tolerance nominal \varnothing	d11
Shank $\varnothing D_s$	6 mm
Direction of infeed	horizontal, oblique and vertical

Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Milling profile	WR
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	270 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable only under restricted conditions	180 m/min	N
Cu	Suitable	80 m/min	N
CuZn	Suitable	100 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	Suitable only under restricted conditions		