

Garant
GARANT Master Tap machine tap Form B 6HX DIN 376, AlTiX, M: M3

Order data

Order number	132726 M3
GTIN	4062406278533
Item class	11I

Description
Version:

Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for a high degree of wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

All sizes: shank to DIN 376 (= shank Ø relieved); thus suitable for greater operating depths.
Without square.

Technical description

Number of cutting edges Z	3
Standard	DIN 376
Thread pitch	0.5 mm
Overall length L	56 mm
Tool material	HSS E PM
Thread Ø	3 mm
Thread type	M
Number of clamping slots	3
Tapping hole Ø	2.5 mm
Tolerance class	ISO 2X 6HX
Shank Ø D _s	2.2 mm

Thread size	M3
Thread depth	9 mm
Coating	AlTiX
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K

CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		