

Garant
NC reamer extra long H7, uncoated, Nominal \varnothing DC: 2mm

Order data

Order number	162971 2
GTIN	4062406264550
Item class	110

Description
Version:

With long flutes and left-hand helix. **Reamers finish ground for fit H7.**

Application:

Especially for deeper holes. Also suitable for blind holes.

Technical description

Number of cutting edges Z	4
Nominal \varnothing D _c	2 mm
Feed f in steel < 750 N/mm ²	0.1 mm/rev.
Tolerance	H7
Shank \varnothing D _s	2 mm
Flute length L _c	11 mm
Shank tolerance	h6
Overhang L ₁	64 mm
Overall length L	85 mm
Reaming oversize in diameter	0.05 - 0.1 mm
Coating	uncoated
Tool material	HSS E
Standard	Manufacturer's standard
Through-coolant	no

Shank	DIN 1835 A to h6
Application for type of drilling	for blind holes and through holes
Colour ring	without
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
Aluminium	suitable	20 m/min	N
Aluminium (short chipping)	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	10 m/min	P
Steel < 900 N/mm ²	suitable	7 m/min	P
Steel < 1100 N/mm ²	suitable	5 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	4 m/min	P
INOX < 900 N/mm ²	suitable	5 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	5 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	5 m/min	S
GG(G)	suitable only under restricted conditions	5 m/min	K
CuZn	suitable only under restricted conditions	13 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		