

## Garant

### Deep hole drill HSS-E, uncoated, Ø DC h8: 3,7mm



#### Order data

Order number	116061 3,7
GTIN	4045197026750
Item class	11B

#### Description

##### Version:

Significantly **strengthened core** without taper.

Precision ground point.

With **specially shaped slots**. Designed for deep holes up to 10×D and materials with critical chip formation characteristics.

##### Recommendation:

##### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

##### Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability.

#### Technical description

Feed f in steel < 500 N/mm <sup>2</sup>	0.05 mm/rev.
Flute length L <sub>c</sub>	73 mm
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	3.7 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	3.7 mm
Overall length L	112 mm
Standard	DIN 340
recommended maximum drilling depth L <sub>2</sub>	67.5 mm

Point angle	130 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	FS
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	45 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	28 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	21 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable	25 m/min	K
Oil	suitable		
wet maximum	suitable		