

Garant
Fluteless machine tap with oil grooves HSS-E-PM Form C 6HX, TiAlN, M: M2,5

Order data

Order number	139171 M2,5
GTIN	4045197541796
Item class	11H

Description
Version:

DIN 2174 (\approx DIN 371 \leq M10; \approx DIN 376 \geq M12). **With oil grooves; optimum lubrication effect even in deeper threads.**

Tolerance class: ISO 2X/6HX.

The **innovative polygon form** permits a wide application spectrum. The **multi-function layer structure** achieves **maximum service life** even in **high-tensile materials**.

Special **TiAlN coating**, highly suitable for **aluminium alloys**.

Tolerance class: ISO 2X 6HX

Thread pitch: 0.45 mm

Overall length L: 50 mm

Shank $\varnothing D_s$: 2.8 mm

Shank square \square : 2.1 mm

Tapping hole \varnothing guide value: 2.3 mm

Technical description

Thread \varnothing	2.5 mm
Number of cutting edges Z	3
Thread pitch	0.45 mm
Number of clamping slots	3
Shank $\varnothing D_s$	2.8 mm
Shank square \square	2.1 mm
Overall length L	50 mm
Tapping hole \varnothing guide value	2.3 mm

Tolerance class	ISO 2X 6HX
Thread depth	7.5 mm
Thread size	M2.5
Coating	TiAlN
Thread type	M
Flank angle	60 °
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Colour ring	yellow
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	42 m/min	N
Aluminium (short chipping)	suitable	42 m/min	N
Alu > 10% Si	suitable	28 m/min	N
Steel < 500 N/mm ²	suitable	32 m/min	P
Oil	suitable		
wet maximum	suitable		