

**Garant**
**Solid carbide micro slot drill, Diamond, Ø DC × L1: 0,1X0,5mm**

**Order data**

|              |                |
|--------------|----------------|
| Order number | 209700 0,1X0,5 |
| GTIN         | 4045197916846  |
| Item class   | 10Y            |

**Description**
**Version:**

With **crystalline diamond sp<sup>3</sup> coating**. For the **highest demands regarding performance and precision** in fibre-reinforced composites, CRP, GRP, and graphite. **Extremely tight tolerances** ensure maximum accuracy. Double relief ground with 2 hollow-ground chamfers. **Recess angle  $\alpha = 16^\circ$** .

Tolerances:

· **Neck Ø:  $D_1 = 0 / -0.01$  mm.**

**Note:**

At greater tool overhang lengths, use a reduced value for  $a_p$ !

Values for:

slots milled from solid:  $a_p = 0.1 \times D \times a_{p \text{ korr}}$

side milling:  $a_p = 0.2 \times D \times a_{p \text{ korr}}$

**To calculate the feed rate vf please use the actual speed of the machine (the maximum possible speed)!**

e.g:  $vf = 18000 \text{ [rpm]} \times fz \text{ [mm/Z]} \times z$

**Technical description**

|                                         |                                  |
|-----------------------------------------|----------------------------------|
| Direction of infeed                     | horizontal, oblique and vertical |
| Feed $f_z$ for slot milling in graphite | 0.008 mm                         |
| Overall length L                        | 45 mm                            |
| No. of teeth Z                          | 2                                |
| Shank                                   | DIN 6535 HA to h5                |
| Cutting edge Ø $D_c$                    | 0.1 mm                           |

|                                           |                             |
|-------------------------------------------|-----------------------------|
| Flute length $L_c$                        | 0.15 mm                     |
| Tolerance nominal $\varnothing$           | 0 / -0.005                  |
| Shank $\varnothing D_s$                   | 4 mm                        |
| Overhang length $L_1$ incl. recess        | 0.5 mm                      |
| Recess $\varnothing D_1$                  | 0.08 mm                     |
| Feed $f_z$ for side milling in graphite   | 0.012 mm                    |
| Helix angle                               | 25 degrees                  |
| Correction factor $a_{p\text{ corr}}$     | 1                           |
| Corner chamfer angle                      | 90 degrees                  |
| Coating                                   | Diamond                     |
| Tool material                             | Solid carbide               |
| Standard                                  | Manufacturer's standard     |
| Cutting width $a_e$ for milling operation | 0.5×D for side milling      |
| Cutting width $a_e$ for milling operation | Full slot cutting depth 1×D |
| Through-coolant                           | no                          |
| Colour ring                               | black                       |
| Type of product                           | End / face mill             |

## User data

|                    | Suitability | $V_c$     | ISO code |
|--------------------|-------------|-----------|----------|
| PVDF GF20          | suitable    | 200 m/min | N        |
| POM GF25           | suitable    | 190 m/min | N        |
| PA 66 GF30         | suitable    | 170 m/min | N        |
| PEEK GF30          | suitable    | 150 m/min | N        |
| PTFE CF25          | suitable    | 180 m/min | N        |
| PEEK CF30          | suitable    | 160 m/min | N        |
| Hybrids            | suitable    |           |          |
| Honeycomb sandwich | suitable    | 350 m/min | N        |
| GRP                | suitable    | 190 m/min | N        |

|             |          |           |   |
|-------------|----------|-----------|---|
| GRP, CRP    | suitable | 190 m/min | N |
| Graphite    | suitable | 340 m/min | N |
| wet minimum | suitable |           |   |
| dry         | suitable |           |   |
| Air         | suitable |           |   |