


**HOLEX Pro INOX M solid carbide milling cutter HPC, TiSiN, Ø e8 DC: 10mm**

**Order data**

Order number	202994 10
GTIN	4062406569112
Item class	12Y

**Description**
**Version:**

**Outstanding tool life** in its class for machining **corrosion-resistant steels** thanks to **innovative coating and geometry**. Especially for **stainless steels in the high-performance range**, e.g. duplex. **Optimal metal removal rate** due to **high cutting speeds**.

**Technical description**

Cutting edge Ø D <sub>c</sub>	10 mm
Recess Ø D <sub>1</sub>	9.7 mm
Feed f <sub>z</sub> for side milling in INOX > 900 N/mm <sup>2</sup>	0.055 mm
Flute length L <sub>c</sub>	22 mm
Overall length L	72 mm
Tolerance nominal Ø	e8
Shank	DIN 6535 HB to h6
Shank Ø D <sub>s</sub>	10 mm
Helix angle	38 degrees
No. of teeth Z	4
Direction of infeed	horizontal, oblique and vertical
Overhang length L <sub>1</sub> incl. recess	30 mm
Feed f <sub>z</sub> for slot milling in stainless steel > 900 N/mm <sup>2</sup>	0.04 mm

Corner chamfer width at 45°	0.2 mm
Corner chamfer angle	45 degrees
Series	Pro Inox
Coating	TiSiN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	150 m/min	P
TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	100 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	85 m/min	M

Uni	suitable only under restricted conditions
wet maximum	suitable
wet minimum	suitable
dry	suitable only under restricted conditions
Air	suitable only under restricted conditions