

**HOLEX****LED rechargeable inspection lamp with swan neck, Type: 460****Order data**

Order number	081572 460
GTIN	4062406262020
Item class	02A

**Description****Version:**

Slim rechargeable LED inspection lamp with swan neck and sturdy 200 mm flexible shank. Main lamp steplessly dimmable. Additional spotlight function. The stable magnetic base with an integral suspension hook also allows use as a desk lamp.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Supplied with charging cable and plug-in power supply unit.

**Technical description**

Bulb	LED module
IP Index of Protection	IP 54
Power supply	Rechargeable battery-powered
ATEX zone	no

Type of rechargeable battery	Lithium-ion
Illumination	50 - 500 lm
Overall length	470 mm
Battery capacity	2.6 Ah
Illumination time	2 - 22 h
Battery voltage	3.6 V
Number of rechargeable batteries contained	1
Weight	325 g
Type of product	Inspection lamp