

Garant
Solid carbide ball nose slot drill, uncoated, Ø f8 DC: 20mm

Order data

Order number	207026 20
GTIN	4045197596611
Item class	11X

Description
Version:

Additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium components.

Dimensions similar to **DIN 6527**.

Technical description

Cutting edge Ø D _c	20 mm
No. of teeth Z	2
Overhang length L ₁ incl. recess	50 mm
Recess Ø D ₁	19 mm
Feed f _z for copy milling in short-chipping aluminium	0.2 mm
Shank Ø D _s	20 mm
Overall length L	93 mm
Flute length L _c	25 mm
Helix angle	45 degrees
Radius R	10 mm
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard

Type	W
Tolerance nominal \varnothing	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.03×D for copy milling
Shank	DIN 6535 HA to h6
Balance quality with shank	G 2.5 with HA
Through-coolant	no
Colour ring	yellow
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	230 m/min	N
Aluminium (short chipping)	suitable	180 m/min	N
Alu > 10% Si	suitable	140 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	Suitable	150 m/min	N
PF 31	Suitable	130 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air

suitable only under
restricted conditions

Services

Shank grinding Type HB

129100 HB