

Garant
Solid carbide end mill with internal coolant supply HPC, ZOX, Ø f8 DC: 20mm


Order data

Order number	202553 20
GTIN	4045197454454
Item class	11X

Description

Version:

Sturdy roughing end mills **without** knuckle profile.

With strong core, **special chip breaker recesses** and **large polished flutes**.

Application:

For roughing milling with high demands on the component surface.

Technical description

Feed f_z for side milling in short-chipping aluminium	0.16 mm
Cutting edge Ø D_c	20 mm
Recess Ø D_1	19 mm
Feed f_z for slot milling in short-chipping aluminium	0.12 mm
Overhang length L_1 incl. recess	52 mm
Corner chamfer width at 45°	0.2 mm
No. of teeth Z	4
Shank form	HB
Shank Ø D_s	20 mm
Overall length L	104 mm
Flute length L_c	40 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6

Tolerance nominal Ø	f8
Balance quality with shank	G 2.5 with HB
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	ZOX
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	yes
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable only under restricted conditions	500 m/min	N
Aluminium (short chipping)	suitable	480 m/min	N
Alu > 10% Si	suitable	240 m/min	N
Hybrids	suitable only under restricted conditions	m/min	N
CuZn	Suitable	240 m/min	N
wet maximum	suitable		
wet minimum	suitable		

dry	suitable only under restricted conditions
Air	suitable only under restricted conditions