

Garant

High-precision countersink, long, with 3 drive flats 90°, TiAlN, External Ø Dc: 10,4mm



Order data

Order number	150376 10,4
GTIN	4062406066000
Item class	11M

Description

Version:

All countersinks have 3 cutting edges, radially relief ground. Flutes ground from solid. High-precision countersink, produced to tight manufacturing tolerances similar to DIN335-C, **with long plain shank.**

Special geometry with extremely unequal spacing and matching cutting edge preparation. Newly developed, **special TiAlN coating** for long tool life.

Three **drive flats on the shank** for use in a 3-jaw chuck.

Application:

High-precision countersinks for chatter-free production of **precise, round 90° countersunk surfaces.**

Technical description

Pre-drill Ø	2.5 mm
Feed f in steel < 500 N/mm ²	0.13 mm/rev.
Shank tolerance	h9
smallest countersink Ø for holes from	2.5 mm
Overall length L	107 mm
Shank Ø D _s	6 mm
Number of cutting edges Z	3
External Ø	10.4 mm
for countersunk screws DIN 7991	M5

Coating	TiAlN
Countersink tip angle	90 degrees
Tool material	HSS
Spacing of the countersink cutting edges	unequal spacing
Standard	Manufacturer's standard
Shank	Three clamping flats to h9
Through-coolant	no
Colour ring	green
Type of product	Stepped drill and countersink

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	75 m/min	N
Aluminium (short chipping)	suitable	75 m/min	N
Alu > 10% Si	suitable	50 m/min	N
Steel < 500 N/mm ²	suitable	65 m/min	P
Steel < 750 N/mm ²	suitable	50 m/min	P
Steel < 900 N/mm ²	suitable	30 m/min	P
Steel < 1100 N/mm ²	suitable	18 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
Steel < 55 HRC	Suitable only under restricted conditions	8 m/min	H
INOX < 900 N/mm ²	suitable	16 m/min	M
INOX > 900 N/mm ²	suitable	10 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	12 m/min	S
GG(G)	suitable	25 m/min	K
CuZn	suitable	60 m/min	N

Graphite, GRP, CRP	suitable only under restricted conditions
Uni	suitable
wet maximum	suitable
dry	suitable only under restricted conditions