

**Garant**
**Solid carbide milling cutter, uncoated,  $\varnothing$  h10 DC: 10mm**

**Order data**

Order number	201043 10
GTIN	4045197746191
Item class	11X

**Description**
**Version:**

**Large flutes for unobstructed swarf evacuation.**

Special geometry **for machining aluminium.**

**Application:**

Especially for milling **aluminium, plunging** and **contour milling.**

**Technical description**

Shank	DIN 6535 HA to h6
Direction of infeed	horizontal, oblique and vertical
Tolerance nominal $\varnothing$	h10
Flute length $L_c$	40 mm
Cutting edge $\varnothing D_c$	10 mm
Shank $\varnothing D_s$	10 mm
Feed $f_z$ for slot milling in short-chipping aluminium	0.04 mm
Overall length L	100 mm
No. of teeth Z	1
Helix angle	26 degrees
Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	solid carbide

Standard	Manufacturer's standard
Type	W
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium	Suitable	170 m/min	N
Aluminium (short chipping)	suitable	125 m/min	N
Alu > 10% Si	suitable	100 m/min	N
PMMA acrylic	Suitable	170 m/min	N
PE-HD	Suitable	120 m/min	N
PA 66	Suitable	140 m/min	N
PEEK	Suitable	120 m/min	N
PF 31	Suitable	100 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	170 m/min	N
Cu	Suitable	130 m/min	N
CuZn	Suitable	160 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

