



Morse taper reamer, uncoated, MT: MK0



Order data

Order number	162500 MK0
GTIN	4045197089175
Item class	120

Description

Version:

Straight flutes, with plain shank and square drive.

Application:

For reaming Morse taper sockets from taper holes or stepped holes.

Technical description

Shank square <input type="checkbox"/>	6.2 mm
Overall length L	93 mm
Flute length L _c	61 mm
Coating	uncoated
Tool material	HSS
Standard	DIN 204
Through-coolant	no
Colour ring	without
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Aluminium (short chipping)	suitable
Steel < 500 N/mm ²	suitable
Steel < 750 N/mm ²	suitable
Steel < 900 N/mm ²	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions