

Garant
GARANT Master Tap INOX machine tap HSS-E-PM, TiAlN, G: G5/8

Order data

Order number	133327 G5/8
GTIN	4062406081157
Item class	111

Description
Version:
GARANT Master Tap INOX:

Powerful tap, specially developed for **tapping to high process reliability in stainless and acid-resistant steels** and also **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Advantage:

Particularly strong, optimum self-guidance and **no recutting** when reversed.

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Tool material: HSS E PM

Threads per inch: 14

Thread Ø: 22.91 mm

Overall length L: 125 mm

Shank Ø D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 21 mm

Technical description

Shank square □	14.5 mm
Thread pitch	1.814 mm
Number of cutting edges Z	4

Tapping hole Ø	21 mm
Overall length L	125 mm
Number of clamping slots	4
Thread depth	68.73 mm
Thread Ø	22.91 mm
Shank Ø D _s	18 mm
Tool material	HSS E PM
Threads per inch	14
Thread size	G5/8
Series	Master Tap
Coating	TiAlN
Thread type	G
Flank angle	55 °
Standard	DIN 5156
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		