

Garant**Countersink set, extra long, No. 150372 in a case 90°, Number of countersinks: 6**

Order data

Order number	150374 6
GTIN	4045197086242
Item class	11M

Description

Version:

Handy for assembly and workshop use.

Countersink No. 150372, **with extra-long shank.****Content:**

1× each countersink: Size 6.3; 8.3; 10.4; 12.4; 16.5; 20.5

Supplied with:

6-piece countersink set in a case.

Technical description

Number of countersinks	6
Number of cutting edges Z	3
Countersink tip angle	90 degrees
Tool material	HSS
Standard	Manufacturer's standard

Shank	Plain shank with h9
Colour ring	without
Type of product	Stepped drill and countersink

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	33 m/min	N
Alu > 10% Si	suitable only under restricted conditions	20 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable	27 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	27 m/min	P
wet maximum	suitable		
dry	suitable only under restricted conditions		

Accessories

High-precision countersink, extra long90° External Ø Dc 8,3 mm	150372 8,3
High-precision countersink, extra long90° External Ø Dc 12,4 mm	150372 12,4
High-precision countersink, extra long90° External Ø Dc 20,5 mm	150372 20,5
High-precision countersink, extra long90° External Ø Dc 16,5 mm	150372 16,5
High-precision countersink, extra long90° External Ø Dc 6,3 mm	150372 6,3
	150372 10,4

High-precision countersink, extra long 90° External Ø Dc
10,4 mm
