

Garant
GARANT Diabolo solid carbide ball nose milling cutter HPC, TiAlN, Ø DC: 10mm

Order data

Order number	207424 10
GTIN	4045197600486
Item class	11X

Description
Version:

Special geometry, coating and carbide for hard machining.

3 end face edges up to the centre. Can therefore be used as a true 3-flute drill in all cutting depths.

Tolerance: Radius contour = ± 0.005 mm.

Technical description

Feed f_z for side milling in steel < 65 HRC	0.07 mm
Feed f_z for copy milling in steel < 65 HRC	0.07 mm
No. of teeth Z	3
Cutting edge $\varnothing D_c$	10 mm
Shank $\varnothing D_s$	10 mm
Overall length L	100 mm
Flute length L_c	18 mm
Helix angle	30 degrees
Radius R	5 mm
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide

Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.2×D for side milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	red
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	200 m/min	P
Steel < 50 HRC	suitable	190 m/min	H
Steel < 55 HRC	suitable	170 m/min	H
Steel < 60 HRC	suitable	150 m/min	H
Steel < 65 HRC	suitable	110 m/min	H
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------