

Garant

GARANT Master Titan solid carbide milling cutter with more chip separators TPC, TiAlN, Ø e8 DC: 4mm



Order data

Order number	203123 4
GTIN	4062406120122
Item class	11Z

Description

Version:

High-performance milling cutter specially designed for general-purpose TPC applications. Strengthened core.

Optimised bending strength due to the use of ultra-fine grain substrates.

Application:

Especially for milling **titanium and titanium alloys**.

Note:

h_{max} : The values stated in the table are maximum values.

$a_{e,max}$: = $0.06 \times D$ for TPC machining.

Technical description

Cutting edge Ø D_c	4 mm
Balance quality with shank	G 2.5 with HB
Shank Ø D_s	6 mm
Direction of infeed	horizontal and oblique
No. of teeth Z	6
Helix angle	40 degrees
Flute length L_c	16 mm
Recess Ø D_1	3.9 mm
Overhang length L_1 incl. recess	23 mm

Average chip thickness h_{\max} for TPC milling in titanium > 850 N/mm ²	0.03 mm
Overall length L	62 mm
Shank	DIN 1835 B to h5
Tolerance nominal \varnothing	e8
Corner rounding r_v	0.1 mm
Series	Master Titan
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.06×D
Through-coolant	no
Machining strategy	TPC
Colour ring	pink
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Ti > 850 N/mm ²	suitable	120 m/min	S
wet maximum	suitable		