

Garant**Die HSS, MF: 26X1****Order data**

Order number	141050 26X1
GTIN	4062406222345
Item class	11K

Description**Version:**Closed, pre-slit form, **with tapered lead chamfer on both sides.****1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 1 mm

External Ø: 55 mm

Height: 16 mm

Technical description

Tolerance class	DIN 13 6g
Pitch	1 mm
External Ø	55 mm
Height	16 mm
Thread size	M26×1

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		