



Solid carbide mini milling cutter, uncoated, Ø e8 DC: 1,8mm



Order data

Order number	202266 1,8
GTIN	4045197864680
Item class	12X

Description

Version:

Shank similar to **DIN 6535 HB**.

Save on regrinding costs:

It is cheaper to use solid carbide mini milling cutters to the wear limit than to regrind them.

Technical description

Tolerance nominal Ø	e8
Cutting edge Ø D _c	1.8 mm
Shank	Parallel shank to h6
Feed f _z for slot milling in steel < 750 N/mm ²	0.005 mm
No. of teeth Z	3
Shank Ø D _s	3 mm
Overall length L	38 mm
Feed f _z for side milling in steel < 750 N/mm ²	0.006 mm
Flute length L _c	3 mm
Direction of infeed	horizontal, oblique and vertical
Shank form	HA
Helix angle	45 degrees
Corner chamfer angle	90 degrees

Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	100 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	60 m/min	P
Steel < 900 N/mm ²	suitable	45 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable only under restricted conditions	55 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	Suitable		
dry	suitable only under restricted conditions		
Air	Suitable		

