

Garant
GARANT Master Steel PickPocket solid carbide roughing end mill HPC, TiAlN, Ø f8 DC: 12mm

Order data

Order number	202404 12
GTIN	4045197781253
Item class	11X

Description
Version:

For **roughing and finishing**

With corner radii similar to torus cutters.

Up to 1×D into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Feed f_z for slot milling in steel < 900 N/mm ²	0.07 mm
Feed f_z for side milling in steel < 900 N/mm ²	0.09 mm
Shank	DIN 6535 HB to h6
Direction of infeed	horizontal, oblique and vertical
Tolerance nominal Ø	f8
Cutting edge Ø D_c	12 mm
Recess Ø D_1	11.8 mm
Overall length L	83 mm
Overhang length L_1 incl. recess	36 mm
No. of teeth Z	3
Shank Ø D_s	12 mm

Flute length L_c	26 mm
Helix angle	38 degrees
Corner rounding r_v	0.6 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.4×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	260 m/min	P
Steel < 750 N/mm ²	suitable	240 m/min	P
Steel < 900 N/mm ²	suitable	190 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P
INOX < 900 N/mm ²	suitable	80 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable