

Garant

GARANT Master Titan solid carbide milling cutter with more chip separators TPC, TiAlN, Ø e8 DC: 6mm



Order data

Order number	203124 6
GTIN	4062406120221
Item class	11Z

Description

Version:

High-performance milling cutter specially designed for general-purpose TPC applications. Strengthened core.

Optimised bending strength due to the use of ultra-fine grain substrates.

Application:

Especially for milling **titanium and titanium alloys**.

Note:

h_{max} : The values stated in the table are maximum values.

$a_{e,max}$: = $0.04 \times D$ for TPC machining.

Technical description

Shank Ø D _s	6 mm
Direction of infeed	horizontal and oblique
Tolerance nominal Ø	e8
Flute length L _c	24 mm
Cutting edge Ø D _c	6 mm
No. of teeth Z	6
Shank	DIN 1835 B to h5
Overall length L	67 mm
Helix angle	40 degrees

Balance quality with shank	G 2.5 with HB
Average chip thickness h_{\max} for TPC milling in titanium > 850 N/mm ²	0.032 mm
Corner rounding r_v	0.1 mm
Series	Master Titan
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.04×D
Through-coolant	no
Machining strategy	TPC
Colour ring	pink
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Ti > 850 N/mm ²	suitable	100 m/min	S
wet maximum	suitable		