

**Garant**
**Solid carbide jobber drill, uncoated, Ø DC h7: 6,4mm**

**Order data**

Order number	122250 6,4
GTIN	4045197041791
Item class	11E

**Description**
**Version:**
**Similar to DIN 338.**

Nominal Ø and shank Ø equal.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Non slip clamping in drill chuck No. 341050 with diamond coated jaws.

**Technical description**

Feed f in steel < 1100 N/mm <sup>2</sup>	0.11 mm/rev.
Nominal Ø D <sub>c</sub>	6.4 mm
Flute length L <sub>c</sub>	63 mm
Number of cutting edges Z	2
Shank tolerance	h7
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	6.4 mm
Overall length L	101 mm
Standard	DIN 338
recommended maximum drilling depth L <sub>2</sub>	53.4 mm
Coating	uncoated
Tool material	Solid carbide

Type	N
Point angle	118 degrees
Helix angle	30 degrees
Shank	Parallel shank to h7
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	200 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	140 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	25 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	20 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	20 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	15 m/min	S
CuZn	suitable	140 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		

dry

suitable only under  
restricted conditions