

Garant
Solid carbide forward / reverse deburring tool, TiAlN, Ø DC: 7,8mm

Order data

Order number	208185 7,8
GTIN	4062406131357
Item class	11X

Description
Version:
Extra long shank.

Double ground head **with 45° angle.**

Application:

For **universal application** in virtually all materials. The newly developed coating **effectively prevents formation of built-up edges** – even in aluminium and stainless steel.

For **forward** and **reverse deburring** and **chamfering** even where access is difficult.

Particularly suitable for **contouring applications.**

Technical description

Ø D ₁ +0.05	6 mm
No. of teeth Z	5
Shank Ø D _s	8 mm
Feed f _z for side milling in steel < 900 N/mm ²	0.012 mm
L ₄ +0.5	26 mm
L ₂ +0.5	2 mm
Overall length L	100 mm
Shape	flat
Corner chamfer angle	45 degrees
Cutting edge Ø D _c	7.8 mm
Chamfer mill	backwards and forwards 45

Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal \varnothing	± 0.05
Countersink tip angle	90 degrees
Cutting width a_e for milling operation	0.25xL2 for side milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Shank tolerance	h6
Colour ring	green
Type of product	Deburrers

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable	125 m/min	N
Alu > 10% Si	suitable	75 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	70 m/min	P
Steel < 900 N/mm ²	suitable	45 m/min	P
Steel < 1100 N/mm ²	suitable	40 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	30 m/min	M
GG(G)	suitable	45 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable
Air	suitable
Services	

Shank grinding Type HB	129100 HB
------------------------	-----------