

Garant
Through hole machine taps + tapping drills, for metric threads: M3-12

Order data

Order number	146450 M3-12
GTIN	4045197085115
Item class	11K

Description
Version:

When the case is opened, the tools raise up vertically and can easily be selected.

Consisting of machine taps M3; M4; M5; M6; M8; M10; M12 and tapping drills size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2.

Content:

1 pc. each machine tap M3 – M10 No. 131150, 1 machine tap M12 No. 131200 and tapping drill No. 114150

Technical description

for metric threads	M3 – M12
Thread type	M
Flank angle	60 degrees
Standard	DIN 371
Standard	DIN 376
Type of product	Tap

Accessories

HSS jobber drillN Ø DC h8 (mm or inch) 6,8	114150 6,8
HSS jobber drillN Ø DC h8 (mm or inch) 3,3	114150 3,3
Machine tapForm B DIN 371 M M4	131150 M4
Machine tapForm B DIN 371 M M3	131150 M3
HSS jobber drillN Ø DC h8 (mm or inch) 10,2	114150 10,2
HSS jobber drillN Ø DC h8 (mm or inch) 4,2	114150 4,2
Machine tapForm B DIN 371 M M5	131150 M5
Machine tapForm B DIN 371 M M10	131150 M10
Machine tapForm B DIN 371 M M6	131150 M6
Machine tapForm B DIN 376 M M12	131200 M12
T-tap wrench with ratchet Overall length 85 mm	148700 85
HSS jobber drillN Ø DC h8 (mm or inch) 2,5	114150 2,5
Machine tapForm B DIN 371 M M8	131150 M8
HSS jobber drillN Ø DC h8 (mm or inch) 8,5	114150 8,5
HSS jobber drillN Ø DC h8 (mm or inch) 5	114150 5
Empty case Type 4	146960 4