

Garant
GARANT Diabolo solid carbide torus cutter HPC, TiAlN, Ø e8 DC / R1: 6/0,8mm

Order data

Order number	206322 6/0,8
GTIN	4045197598264
Item class	11X

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide, specially for hard machining.

Double relief ground side clearance angle.

Tolerance: Corner radius $R_1 = \pm 0.005 \text{ mm}$.

Technical description

Feed f_z for copy milling in steel < 65 HRC	0.048 mm
No. of teeth Z	4
Recess $\varnothing D_1$	5.5 mm
Overhang length L_1 incl. recess	21 mm
Corner radius R_1	0.8 mm
Feed f_z for side milling in steel < 65 HRC	0.048 mm
Cutting edge $\varnothing D_c$	6 mm
Shank $\varnothing D_s$	6 mm
Flute length L_c	7 mm
Overall length L	57 mm
Shank	DIN 6535 HA to h6
Helix angle	30 degrees
Series	Diabolo

Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	e8
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.2×D for side milling
Cutting width a_e for milling operation	0.05×D for copy milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	200 m/min	P
Steel < 50 HRC	suitable	190 m/min	H
Steel < 55 HRC	suitable	170 m/min	H
Steel < 60 HRC	suitable	150 m/min	H
Steel < 65 HRC	suitable	110 m/min	H
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB