

Garant**GARANT Master Tap machine tap HSS-E-PM Form B 6HX left-hand thread, ALTiX, MF-LH: 12X1,25****Order data**

Order number	133015 12X1,25
GTIN	4045197901477
Item class	11I

Description**Version:**

GARANT Master Tap Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Thread type: MF-LH

Tool material: HSS E PM

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 1.25 mm

Overall length L: 100 mm

Shank Ø D_s: 9 mm

Shank square □: 7 mm

Tapping hole Ø: 10.8 mm

Technical description

Tapping hole Ø	10.8 mm
Number of clamping slots	3
Thread depth	36 mm
Thread type	MF-LH
Overall length L	100 mm

Shank square ☐	7 mm
Standard	DIN 374
Thread Ø	12 mm
Number of cutting edges Z	3
Tolerance class	ISO 2X 6HX
Thread size	M12×1.25 LH
Thread pitch	1.25 mm
Shank Ø D _s	9 mm
Tool material	HSS E PM
Coating	AlTiX
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P

Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		