

**HSS jobber drill N, uncoated, Ø DC h8: 20mm****Order data**

Order number	116320 20
GTIN	4045197029638
Item class	12C

Description**Version:**

Special surface treatment, resulting in reduced tendency to edge build-up **and improved chip evacuation.**

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530.**

Technical description

Nominal Ø D _c	20 mm
Flute length L _c	140 mm
Feed f in steel < 750 N/mm ²	0.2 mm/rev.
Number of cutting edges Z	2
Tolerance nominal Ø	h8
Overall length L	238 mm
Morse taper MT size	2
Standard	DIN 345
recommended maximum drilling depth L ₂	110 mm
Point angle	118 degrees
Shank	Morse taper

Coating	uncoated
Tool material	HSS
Type	N
Helix angle	20-30 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		