



Magnetic measuring stand with fine adjustment at the column, Type: 120SF



Order data

Order number	441 180 120SF
GTIN	4045197713186
Item class	42D

Description

Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Standard dial indicator mounting for clamping shank \varnothing 6 mm, \varnothing 8 mm and dovetail, fine adjustment at the indicator holder.

Technical description

Length of jointed arm L_2	51 mm
Length of jointed arm L_1	56 mm
Magnetic force	320 N
Magnetic base width	30 mm
maximum loading	2.7 kg
Throat	178 mm
Magnetic base height	36 mm

Magnetic base length	36 mm
Connection thread at bottom	M5
Type of product	measuring stand

Accessories

Holder for measuring stand Type H	442100 H
3-D jointed arm Type 120	442114 120
Holder for measuring stand Type 2SM	442100 2SM
Stand base Type S	442140 S
3-D jointed arm Type 120	442110 120
Stand base Type S	442120 S
Stand base with fine adjustment Type S	442125 S
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type K1	442100 K1
Holder for measuring stand Type QR	442100 QR
Holder for measuring stand Type CA	442100 CA
Holder for measuring stand Type K2	442100 K2