



Magnetic measuring stand with fine adjustment at the column, Type: 290



Order data

Order number	441180 290
GTIN	4045197713308
Item class	42D

Description

Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Standard dial indicator mounting for clamping shank \varnothing 6 mm, \varnothing 8 mm and dovetail, fine adjustment at the indicator holder.

Technical description

Magnetic base width	50 mm
Length of jointed arm L_2	129 mm
Magnetic base height	55 mm
Magnetic base length	80 mm
Throat	349 mm
Length of jointed arm L_1	149 mm

Magnetic force	800 N
maximum loading	8 kg
Connection thread at bottom	M8
Type of product	measuring stand

Accessories

Holder for measuring stand Type 2SM	442100 2SM
Stand base Type 1	440868 1
Stand base Type V	442120 V
Stand base Type K3	442120 K3
Stand base Type 0	442120 0
Holder for measuring stand Type QR	442100 QR
Stand base Type 0	442140 0
Holder for measuring stand Type K2	442100 K2
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type H	442100 H
Stand base Type 1	442120 1
3-D jointed arm Type 290	442110 290
Stand base Type 1	442140 1
Holder for measuring stand Type K1	442100 K1
Holder for measuring stand Type CA	442100 CA
3-D jointed arm Type 290	442114 290
Stand base with fine adjustment Type 0	442125 0