

Garant**GARANT Master Tap INOX machine tap HSS-E-PM Form B 6HX, TiAlN, M: M10****Order data**

Order number	132180 M10
GTIN	4062406080792
Item class	11I

Description**Version:**

High-performance tap, specially developed for **good process reliability in stainless and acid-resistant steels** and **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank Ø D_s: 10 mm

Shank square □: 8 mm

Tapping hole Ø: 8.5 mm

Technical description

Thread pitch	1.5 mm
Number of clamping slots	3
Number of cutting edges Z	3
Shank square □	8 mm
Standard	DIN 371
Thread Ø	10 mm

Overall length L	100 mm
Shank Ø D _s	10 mm
Tool material	HSS E PM
Tapping hole Ø	8.5 mm
Tolerance class	ISO 2X 6HX
Thread type	M
Thread depth	30 mm
Thread size	M10
Coating	TiAlN
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P

INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		