

Garant**Die HSS, MF: 4X0,25****Order data**

| | |
|--------------|---------------|
| Order number | 141050 4X0,25 |
| GTIN | 4062406223045 |
| Item class | 11K |

Description**Version:**Closed, pre-slit form, **with tapered lead chamfer on both sides.****1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.25 mm

External Ø: 20 mm

Height: 5 mm

Technical description

| | |
|-----------------|-----------|
| Tolerance class | DIN 13 6g |
| Height | 5 mm |
| External Ø | 20 mm |
| Pitch | 0.25 mm |
| Thread size | M4×0.25 |

| | |
|-------------------|------------|
| Thread type | MF |
| Flank angle | 60 ° |
| Tool material | HSS |
| Standard | EN 22568 |
| Cutting direction | right-hand |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |