

Garant

**Carbide boring bar E.. SVUBR 93°, for indexable inserts VB., right-hand,
Shank Ø / insert size: 16/11mm**

**Order data**

Order number	261118 16/11
GTIN	4062406099107
Item class	21T

Technical description

Insert size	11 mm
Pack of insert screws	269028 7
ISO code toolholder	E16R SVUBR/L 11
suitable indexable insert	VB.. 1103..
Clamping height L_2	15 mm
Centre offset L_3	11 mm
Head length L_1	16.5 mm
Minimum pre-drill $\varnothing D_{\min}$	21 mm
Overall length L	200 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar