

Garant

**Carbide boring bar E.. SVJCR 142°, for indexable inserts VC.., right-hand,
Shank Ø / insert size: 12/07mm**


Order data

Order number	261326 12/07
GTIN	4062406100452
Item class	21T

Technical description

ISO code toolholder	E12M SVJCR/L07
Centre offset L_3	2 mm
Overall length L	150 mm
Neck width L_4	7.8 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
Insert size	7 mm
Head length L_1	18 mm
Setting angle κ	142 degrees
Clamping height L_2	11 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar