



## HOLEX Pro Steel solid carbide roughing end mill HPC, TiAlN, Ø d11 DC: 5mm



### Order data

Order number	205704 5
GTIN	4062406262068
Item class	12X

### Description

#### Version:

Dimensions similar to DIN 6527. **Optimised special knuckle form profile for roughing.** Very **high metal removal rate.**

#### Application:

For roughing machining, particularly suitable for full-slot machining.

### Technical description

Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.02 mm
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	d11
Shank Ø $D_s$	6 mm
Flute length $L_c$	9 mm
Corner chamfer width at 45°	0.25 mm
No. of teeth Z	4
Corner chamfer angle	45 degrees
Helix angle	45 degrees
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.028 mm
Cutting edge Ø $D_c$	5 mm
Overall length L	54 mm

Direction of infeed	horizontal, oblique and vertical
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	135 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	120 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	60 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	45 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air

Suitable only under  
restricted conditions