

**Garant**

**Carbide boring bar E.. SVJCL 142°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 12/07mm**


**Order data**

Order number	261327 12/07
GTIN	4062406100643
Item class	21T

**Technical description**

Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Setting angle $\kappa$	142 degrees
Head length $L_1$	18 mm
Centre offset $L_3$	2 mm
Insert size	7 mm
Clamping height $L_2$	11 mm
Neck width $L_4$	7.8 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
ISO code toolholder	E12M SVJCR/L07
Overall length L	150 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar