

Garant

**Carbide boring bar E.. SVUCR 93°, for indexable inserts VC., right-hand,
Shank Ø / insert size: 20/11mm**


Order data

Order number	261328 20/11
GTIN	4062406100704
Item class	21T

Technical description

Setting angle κ	93 degrees
Head length L_1	20.5 mm
Pack of insert screws	269028 7
Centre offset L_3	13 mm
ISO code toolholder	E20S SVUCR/L11
Clamping height L_2	18 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Overall length L	250 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar