

Garant

Carbide boring bar E.. SVUCL 93°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 20/11mm

**Order data**

Order number	261329 20/11
GTIN	4062406100834
Item class	21T

Technical description

Head length L_1	20.5 mm
Overall length L	250 mm
Clamping height L_2	18 mm
Centre offset L_3	13 mm
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 7
Setting angle κ	93 degrees
ISO code toolholder	E20S SVUCR/L11
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar