

Garant
**GARANT Master Titan solid carbide ball nose milling cutter HPC, TiAlN, Ø f8
DC / DS: 6mm**

Order data

Order number	207482 6
GTIN	4045197989604
Item class	11Z

Description
Version:
Special geometry for machining **titanium and titanium alloys**.

4 centre cutting edges to the centre.

 Therefore can be used as a **true 4-edge cutter** at all depths of cut.

 Tolerance: Radius contour = ± 0.005 mm.

Note:

Regrinding not recommended.

Technical description

Feed f_z for copy milling in titanium > 850 N/mm ²	0.024 mm
Flute length L_c	10 mm
Correction factor for v_c	1.25
Overall length L	54 mm
Cutting edge $\varnothing D_c$	6 mm
Shank $\varnothing D_s$	6 mm
No. of teeth Z	4
Feed f_z for side milling in titanium > 850 N/mm ²	0.02 mm
Helix angle	45 degrees
Radius R	3 mm

Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal Ø	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Cutting width a_e for milling operation	$0.05 \times D$ for side milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	pink
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Ti > 850 N/mm ²	suitable	60 m/min	S
wet maximum	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------