

Garant

Shrink-fit chucks with cooling channel bore, HSK-A 100 A = 130, Clamping \varnothing D1: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 308284 10 |
| GTIN | 4062406101404 |
| Item class | 31A |

Description

Version:

From clamping \varnothing D₁ 6 mm with tapped holes for balancing screws.

Integral length adjustment of the tool from clamping \varnothing D₁ 6 mm (adjustment travel 10 mm).

- **High-temperature steel.**
- **Sizes 3 – 5 for carbide, from size 6 for HSS and carbide.**
- **With RFID/Balluffchip bore.**

With **cooling channel bores** tapped for plugging.

GARANT: HSK mating faces machined. **All shanks hard turned (for smooth running!).**

Application:

- **For holding end mills and drills with parallel shank to h6 tolerance.**
- **Suitable for inductive, contact and hot air shrink-fit units.**

Supplied with:

For chucks with length adjustment including a length adjustment screw (from clamping \varnothing D₁ 6 mm).

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, shrink-fit chuck extension No. 302410 – 302416, shrink-fit units No. 354210 – 354450, balancing screw set No. 309906 180.

Technical description

| | |
|------------------------------|----------|
| Cooling channel bore | lockable |
| \varnothing D ₂ | 24 mm |

| | |
|---------------------------------------|----------------------|
| Clamping $\varnothing D_1$ | 10 mm |
| Overhang dimension A | 130 mm |
| External $\varnothing D$ | 32 mm |
| Adapter | HSK-A 100 A = 130 |
| Arbor standard | ISO 12164-1 |
| Arbor standard | DIN 69893 |
| Shape | A |
| Through-coolant | yes |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | $\leq 3 \mu\text{m}$ |
| Machining strategy | HSC |
| Machining strategy | HPC |
| Type of product | Shrink-fit chuck |

Accessories

| | |
|--------------------------|------------|
| Cooling unit Type CU1 | 354215 CU1 |
| Shrink-fit unit Type SU1 | 354210 SU1 |